Product Specifications

PC-UK-120-250

Engine Power Cord for the United Kingdom, Hong Kong, and Singapore

OBSOLETE

General Specifications

Product Type	Power cord
Application	Connects Redwood engine to electrical outlet
Color	Black
Ordering Note	Available in Asia Pacific | Available in Europe, the Middle East and Africa
Package Quantity	1

Dimensions

Length	3050 mm | 120 in
Outer Diameter	8.50 mm | 0.33 in

Mechanical Specifications

Conductor Gauge, stranded	1.5 mm²
Conductors, quantity	3
Jacket Standard	H05VV-F
Material Type	PVC
Power Cord Connector Interface	IEC 60320-C19
Power Cord Plug Standard	BS 1363 (United Kingdom)

Electrical Specifications

Current, maximum	13 A
Input Voltage	250 Vac

Environmental Specifications

Environmental Space	Indoor
Safety Standard	BSI

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 22, 2016

Product Specifications

PC-UK-120-250

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 22, 2016