



760105015 | 360-iP-UP-KIT-1100-48
SYSTIMAX 360™ iPatch® Upgrade Kit for 1100GS 48 Port Panel, 5 pack

OBSOLETE

This product was discontinued on: October 31, 2015

Dimensions

Depth	12.70 mm 0.50 in
Height	31.75 mm 1.25 in
Weight	0.11 kg 0.25 lb
Width	393.70 mm 15.50 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® upgrade kit
Total Ports, quantity	48
Product Type	Panel
Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Color	Cool gray
Package Quantity	5

Mechanical Specifications

Material Type	ABS Polycarbonate
---------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

760105015 | 360-iPUP-KIT-1100-48

