



700016470 | M224CPN-246
M224 Type Zone Box Cover, ivory

General Specifications

Mount Type	Surface
Product Type	Zone box
Application	Provide for the distribution of data and telecommunication signals
Color	Ivory
Package Quantity	1

Dimensions

Depth	36.58 mm 1.44 in
Height	308.36 mm 12.14 in
Weight	0.88 kg 1.95 lb
Width	214.63 mm 8.45 in

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--------------------------------------------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system