

760080820 | MIB-2

**2 Port Industrial Box**

## General Specifications

|                       |                                     |
|-----------------------|-------------------------------------|
| Mount Type            | Surface                             |
| Product Type          | Surface mount box                   |
| Application           | Provides sealed copper connectivity |
| Color                 | Gray                                |
| Package Quantity      | 1                                   |
| Total Ports, quantity | 1                                   |

## Dimensions

|                    |                     |
|--------------------|---------------------|
| Depth              | 82.55 mm   3.25 in  |
| Height             | 119.38 mm   4.70 in |
| Plug Diameter      | 29.21 mm   1.15 in  |
| Receptacle Opening | 27.94 mm   1.10 in  |
| Weight             | 0.54 kg   1.20 lb   |
| Width              | 78.74 mm   3.10 in  |

## Mechanical Specifications

|               |          |
|---------------|----------|
| Material Type | Aluminum |
|---------------|----------|

## Electrical Specifications

|                   |             |
|-------------------|-------------|
| ANSI/TIA Category | 5e   6   6A |
|-------------------|-------------|

## Environmental Specifications

|                         |   |
|-------------------------|---|
| Flammability Rating     | UL 94 V-0                                     |
| Operating Temperature   | -25 °C to +85 °C (-13 °F to +185 °F)          |
| Qualification Standards | IEC 60529: 2001, IP65   IEC 60529: 2001, IP67 |
| Safety Standard         | cUL   UL                                      |

## Regulatory Compliance/Certifications

| Agency          | Classification   |
|-----------------|--|
| RoHS 2011/65/EU | Compliant  |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |