



Cat6 Snagless Cables

- Supports voice/data/video distribution applications up to 500 MHz
- Meets all Cat6 TIA/EIA-568-B.2 standards
- Lifetime Warranty

Specifications: Cat6 Snagless Cables

Electrical Specifications:

Conductor DC Resistance:	9.38Ω/100m (maximum)
Impedance:	100Ω
Capacitance:	5600pf/100m
Propagation Delay:	545ns/100m (maximum)
Delay Skew:	45ns/100m (maximum)

Physical Specifications:

Wiring Scheme:	T568B
Temperature Rating:	75°C
Voltage Rating:	30V
Approvals:	CE
Warranty:	Lifetime
Package Type:	Polybag

Conductor (4 pair):


Conductor:	24AWG (7/0.20 BC)
Insulation:	HD-PE ID: $\varnothing 0.98 \pm 0.05$
Twist Pair:	Orange, White/Orange, Blue, White/Blue, Green, White/Green Brown, White/Brown

Connectors (Qty 2):

Connector Type:	8P8C (RJ45)
Gender:	Male
Contacts:	Gold Plated 50μ
Hood:	Molded PVC, UL94V-0

Overall Cable

Jacket:	PVC
OD:	6.0 ± 0.15



Specifications: Cat6 Snagless Cables

Length	Gray	Blue	Black	Green	Red	Yellow	Orange	Purple	White	Pink
6"	00951	00952	00953	00954	00955	00956	00957	00958	00959	00960
1ft	27130	27140	27150	27170	27180	27190	27810	27800	27160	04043
2ft	03965	03973	03981	03989	03998	04007	04016	04025	04034	04044
3ft	27131	27141	27151	27171	27181	27191	27811	27801	27161	04045
4ft	03966	03974	03982	03990	03999	04008	04017	04026	04035	04046
5ft	31340	31341	31342	31344	31345	31346	31348	31347	31343	04047
6ft	03967	03975	03983	03991	04000	04009	04018	04027	04036	04048
7ft	27132	27142	27152	27172	27182	27192	27812	27802	27162	04049
8ft	03968	03976	03984	03992	04001	04010	04019	04028	04037	04050
9ft	03969	03977	03985	03993	04002	04011	04020	04029	04038	04051
10ft	27133	27143	27153	27173	27183	27193	27813	27803	27163	04052
12ft	03970	03978	03986	03994	04003	04012	04021	04030	04039	04053
14ft	27134	27144	27154	27174	27184	27194	27814	27804	27164	04054
15ft	22016	22015	22014	03995	04004	04013	04022	04031	04040	04055
20ft	03971	03979	03987	03996	04005	04014	04023	04032	04041	04056
25ft	27135	27145	27155	27175	27185	27195	27815	27805	27165	04057
30ft	03972	03980	03988	03997	04006	04015	04024	04033	04042	04058
35ft	31350	31351	31352	31354	31355	31356	31358	31357	31353	04059
50ft	27136	27146	27156	27176	27186	27196	27816	27806	27166	04060
75ft	31360	31361	31362	31364	31365	31366	31368	31367	31363	04061
100ft	27137	27147	27157	27177	27187	27197	27817	27807	27167	04062
150ft	27139	27149	27159	27179	27189	27199	27819	27809	27169	04063

