



BURNDY Catalog Number YGHA282N
UPC Number 781810220375
Description CU 4/0, HVY DUTY GRD TER
Status Active

Web Use
BURNDY Product Line

Dimensional	
Thickness	0.30
B Length (in)	1.18
D - in	3
Pad Width (in)	1.22
Stud Size (Fraction)	1/2
E - in	1.75
General	
Product Description	Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe, 4/0 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG
Physical	
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Index Number	17
Approvals / Certifications	
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B,UL467,IEEE 837
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies
47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175