



BURNDY Catalog Number YGHA2C2N
UPC Number 781810220351
Description CU 2 HVY DUTY GRD TERM 2
Status Active

Web Use
BURNDY Product Line

Dimensional

Thickness 0.26
B Length (in) 0.75
D - in 3
Pad Width (in) 0.97
Stud Size (Fraction) 1/2
E - in 1.75

General

Product Description Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 2 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel

Conductor(s)

Copper Solid Size (Range) N/A
Copper Stranded (Range) 2 AWG

Physical

Type of Plating Unplated
Connector Type Terminal
Plated (Yes or No) N
Index Number 11

Approvals / Certifications

Rated for Direct Burial Y
UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B,UL467,IEEE 837
Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175