



BURNDY Catalog Number	YGHC29C29
UPC Number	781810221051
Description	3/0-250 TO 3/0-250 GRD C
Status	Active

Web Use
BURNDY Product Line

Dimensional	
B Length (in)	0.88
Diameter (in) - Total	2.06
General	
Product Description	Copper Compression C Connector, 3/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 3/0 AWG(Str) - 250 kcmil (Tap)
Conductor(s)	
Copper Tap Range	3/0 AWG-250 kcmil
Copper Stranded Run (Range)	3/0 AWG-250 kcmil
Rod Size Run (Range)	1/2 in-5/8 in
Copper Solid Tap (Range)	N/A
Rebar Run Size (Range)	N/A
Copper Solid Run Size (Range)	N/A
Physical	
Type of Plating	Unplated
Connector Type	Tap
Plated (Yes or No)	N
Index Number	997
Product Material	Copper
Approvals / Certifications	
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B,UL467,IEEE 837
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies
47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175