



QCPC-6ARSZB-BL03M | 300001779385

**Quareo® Q2000 Series Managed Copper Patch Cord, Category 6A S/FTP, LSZH, T568B, 3 m, blue**

- Designed with integrated strain relievers, safeguarding circuit integrity
- Impedance matched for use in Quareo structured cabling systems
- Using Quareo Technology with connection point identification

## Body Features

Cable Color	Blue
Shield Style	S/FTP
Boot Type	Flexible strain relief
Cable Construction	PVC stranded
Conductor Material	Copper

## Configuration Features

Wiring Pattern	Crossover
Keyed	No

## Dimensions

Length	3.00 m   9.84 ft
--------	------------------

## Industry Standards

Flammability Rating	UL94-V0
Standards Compliance	ANSI/TIA/EIA-968-A   CE   IEC 60603-7   TICK N355

## Packaging Features

Packaging Method	Bag
Packaging Quantity	1

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
Comments	Standard colors: blue, gray and white (other colors are available upon request)   Standard lengths: 1, 2, 3, 5, 10 and 15 meters (other lengths available upon request)

## Product Type Features

Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6A
Product Type	Cable Assembly
System	Managed Connectivity

## Usage Conditions

# Product Specifications



QCPC-6ARSZB-BL03M | 300001779385

Operating Temperature      -10 – 60 °C | 14 – 140 °F  
Relative Humidity (Operating) 5%  
Relative Humidity (Storage) 5%  
Storage Temperature        0 – 50 °C | 32 – 122 °F

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant