

J-HOOKS - Cable management that's fast and secure.

J-Hooks provide an easy-to-install, non-continuous cable support for all types of telecommunication, data and power cabling. They also are perfect for low voltage building management and fire protection cabling.

Our CJ Series is engineered to provide stress-free cable support for multiple cables and features a structural design for optimal strength and tapered edges to reduce cable sheath damage. Multiple pre-drilled holes reduce on-site modification at installation. J-Hooks can be attached to a variety of structures and are available with multiple attachment options that allow quick and easy cable installation virtually anywhere.

The CJHP Series J-Hooks are plastic coated and feature a built in latch that allows you to lock the bendable flap into place – up to 50 times with no signs of metal fatigue. CJHP hooks combine the best features of both metal and plastic, providing strength and a slick, no-bur surface to make pulling cable easy. All CJHP hooks are plenum safe.



FEATURES

- Broad product line
- Sturdy steel construction
- Smooth tapered edges
- UL load tested
- Simple one person installation
- Engineered for the future
- RoHS compliant
- Recyclable and produced with over 30% recycled steel
- No bonding/grounding needed
- Meets TIA-568-C & TIA 569-C and complies with EN 50174-2

BENEFITS

- CJ hooks are available in ¾" to 4" sizes with multiple attachment options; CJHP hooks are available in 1" to 3" sizes with two attachment options
- Provides optimal support for electrical and high-performance data cables (Including Cat 5e, Cat 5, Cat 6A, Cat 7, and fiber optic)
- Reduces pressure points for ultimate cable protection
- cULus listed
- · Labor savings
- Accommodates future emerging data cables
- Environmentally friendly
- · Great for the environment
- Cost savings
- Ensures that software and applications running on the network are able to perform as designed and work seamlessly together

COMPLIANCE






CABLOFIL® FASTENERS J-Hooks







	CJ Load Capacity Table							
	HOOK SIZE	LOAD CAPACITY	CABLE CAPACITY					
	IN	LBS	4-PAIR UTP CAT 5E	CAT 6	2 STRAND FIBER OPTIC			
CJ12	3/4	17	16	10	16			
CJ21	1 5/16	17	50	32	50			
CJ32	2	17	80	50	80			
CJ64	4	50	300	185	300			

		CJ Attachment Options		
W	AC	AC6	HOK24	HOK58
			HON-26	
Bat wing 12 gage – 1/4" ATR	90° angled clip – ½" hole	90° angled clip – ³ ⁄8" hole	Knock-on steel beam clamp – 1/8" to 1/4"	Knock-on steel beam clamp – 5/16" to ½"
PBC	СРВС	SSBC	ACSSB	ACHOK24
Pressed beam clamp – up to ½"	Angled clip and pressed beam clamp – up to ½"	Assembled to SSBC – 1/8" to 1/2"	Angled clip and SSBC – swivels 360°	Knock-on clamp and angled clip – swivels 360°

PART NUMBERING EXAMPLE CJ12HOK24						
J-HOOK	ATTACHMENT					
Choose between CJ12, CJ21, CJ32 & CJ64	Choose option					

CJ12 – ¾" J-HOOK						
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ	
CJ12	50	3/4	Basic J-Hook	2.5	F000001	
CJ12W	50	3/4	J-Hook w/ Bat Wing	3.5	F000002	
CJ12AC	50	3/4	J-Hook w/ 90 Degree Angle Clip	4	F000003	
CJ12HOK-24	50	3/4	J-Hook w/ Knock on Steel Beam Clamp - 1/8" to 1/4"	5	F000004	
CJ12HOK-58	50	3/4	J-Hook w/ Knock on Steel Beam Clamp - 5/16" to 1/2"	5	F000005	
CJ12PBC	50	3/4	J-Hook w/ Pressed Beam Clamp	8.5	F000006	
CJ12CPBC	50	3/4	J-Hook w/ Angled Clamp and Pressed Beam Clamp	10	F000007	
CJ12SSB	50	3/4	J-Hook w/ assembled to SSBC	5.5	F000008	
CJ12CSSB	50	3/4	J-Hook w/ angle clip and SSBC - swivels 360°	7	F000009	
CJ12ACOK24	50	3/4	J-Hook w/ hammer on and angle clip – swivels 360°	6.5	F000010	

CJ21 – 1 ⁵ / ₁₆ " J-HOOK							
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ		
CJ21	50	⁵ /16	Basic J-Hook	6.5	F000011		
CJ21W	50	5/16	J-Hook w/ Bat Wing	7.5	F000012		
CJ21AC	50	5/16	J-Hook w/ 90 Degree Angle Clip	8.5	F000013		
CJ21HOK-24	50	⁵ /16	J-Hook w/ Knock on Steel Beam Clamp - 1/8" to 1/4"	9	F000014		
CJ21HOK-58	50	⁵ /16	J-Hook w/ Knock on Steel Beam Clamp - 5/16" to 1/2"	9	F000015		
CJ21PBC	50	5/16	J-Hook w/ Pressed Beam Clamp	12.5	F000016		
CJ21CPBC	50	5/16	J-Hook w/ Angled Clamp and Pressed Beam Clamp	14	F000017		
CJ21SSB	50	⁵ /16	J-Hook w/ assembled to SSBC	9.5	F000018		
CJ21CSSB	50	5/16	J-Hook w/ angle clip and SSBC – swivels 360°	11.5	F000019		
CJ21ACOK24	50	5/16	J-Hook w/ hammer on and angle clip – swivels 360°	11.5	F000020		


CJ32 – 2" J-HOOK						
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ	
CJ32	50	2	Basic J-Hook	7.5	F000021	
CJ32W*	50	2	J-Hook w/ Bat Wing	8.5	F000022	
CJ32AC	50	2	J-Hook w/ 90 Degree Angle Clip	8.5	F000023	
CJ32HOK-24	50	2	J-Hook w/ Knock on Steel Beam Clamp - 1/8" to 1/4"	9.5	F000024	
CJ32HOK-58	50	2	J-Hook w/ Knock on Steel Beam Clamp - 5/16" to 1/2"	10	F000025	
CJ32PBC	50	2	J-Hook w/ Pressed Beam Clamp	13.5	F000026	
CJ32CPBC	50	2	J-Hook w/ Angled Clamp and Pressed Beam Clamp	15	F000027	
CJ32SSB	50	2	J-Hook w/ assembled to SSBC	10.5	F000028	
CJ32CSSB	50	2	J-Hook w/ angle clip and SSBC - swivels 360°	12.5	F000029	
CJ32ACOK24	50	2	J-Hook w/ hammer on and angle clip - swivels 360°	12.5	F000030	

^{*} Works with both 1/4 x 20 and 3/8 x 16 rod


	CJ64 – 4" J-HOOK						
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ		
CJ64	25	4	Basic J-Hook	7.5	F000031		
CJ64W	25	4	J-Hook w/ Bat Wing	8.5	F000032		
CJ64AC	25	4	J-Hook w/ 90 Degree Angle Clip – 1/4" hole	12.5	F000039		
CJ64HOK-24	25	4	J-Hook w/ Knock on Steel Beam Clamp - 1/8" to 1/4"	9.5	F000033		
CJ64HOK-58	25	4	J-Hook w/ Knock on Steel Beam Clamp – 5/16" to 1/2"	10	F000034		
CJ64PBC	25	4	J-Hook w/ Pressed Beam Clamp	13.5	F000035		
CJ64CPBC	25	4	J-Hook w/ Angled Clamp and Pressed Beam Clamp	15	F000036		
CJ64SSB	25	4	J-Hook w/ assembled to SSBC	10.5	F000037		
CJ64CSSB	25	4	J-Hook w/ angle clip and SSBC - swivels 360°	12.5	F000038		
CJ64AC6	25	4	J-Hook w/ 90 Degree Angle Clip – 3/8" hole	12.5	F000040		
CJ64ACOK24	25	4	J-Hook w/ hammer on and angle clip – swivels 360°	12.5	F000041		




CABLOFIL® FASTENERS J-Hooks



CJP Load Capacity Table							
	HOOK SIZE	LOAD CAPACITY	CABLE CAPACITY				
	IN	LBS	4-PAIR UTP CAT 5E	CAT 6	2 STRAND FIBER OPTIC		
CJ16HP	1	17	20	15	20		
CJ32HP	2	17	90	60	90		
CJ48HP	3	50	200	150	200		



CJ16HP



CABLOFIL® FASTENERS J-Hooks



	CJ16HP							
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ			
CJ16HP	50	1	Basic Plastic Coated CJP Hook w/Latch	2.5	F000051			
	50	1	Plastic Coated CJP Hook w/Latch and Bat Wing Clip	4				
	50	1	Plastic Coated CJP Hook w/Latch and Angled Wing Clip	5				

CJ32HP							
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ		
CJ32HP	50	2	Basic Plastic Coated CJP Hook w/Latch	5	F000052		
	50	2	Plastic Coated CJP Hook w/Latch and Bat Wing Clip				
	50	2	Plastic Coated CJP Hook w/Latch and Angled Wing Clip	6.5			

	CJ64HP						
	PKG QTY	HOOK SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ		
CJ64HP	50	3	Basic Plastic Coated CJP Hook w/Latch	15.5	F000053		
	50	3	Plastic Coated CJP Hook w/Latch and Bat Wing Clip	18			
	50	3	Plastic Coated CJP Hook w/Latch and Angled Wing Clip	17.5			

BRIDLE RINGS

Bridle rings are a simple option for smaller bundles of communication or data cabling.

	PKG QTY	RING SIZE (IN)	DESCRIPTION	WEIGHT (LBS)	EZ
CJ4T125	100	1 1/4	Bridle Ring ¼ x 20	6	F000042
CJ4T2	100	2	Bridle Ring ¼ x 20	9	F000043

