



760236108 | DM08-24LC-LS-ULL

G2 ULL MPO-8 Distribution Module, 3x8F MPO unpinned to 24F LC Aqua, Method B Enhanced, OM4

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber (OM4)
Total Fibers, quantity	24

Dimensions

Depth	117.35 mm 4.62 in
Height	26.42 mm 1.04 in
Width	96.52 mm 3.80 in

Environmental Specifications

Safety Standard	cUL US 1863
-----------------	-------------

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Aqua
Adapters, quantity, front	12
Brand	SYSTIMAX ULL SYSTIMAX®
Data Module Type	G2
Shuttered	Yes
Interface, rear	MPO Unpinned
Adapters, quantity, rear	3
Interface Feature, rear	Key up
Color, rear	Aqua
Package Quantity	1

Optical Performance

Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.35 dB

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU
ISO 9001:2008

Classification

* Footnotes

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)