



CISCO AIR-ANT2566P4W-R PATCH ANTENNA ARTICULATING MOUNT



The AccelTex Solutions articulating mount for the Cisco AIR-ANT2566P4W-R allows installers to articulate the antenna horizontally and vertically to cover a specified area. This heavy duty mount is suitable for a wall, ceiling or pole installation and with the inscribed degree markings, provides maximum and precise articulation for the antenna.

Part Number: ATS-ANTMNT-HDART2566P

> MECHANICAL SPECIFICATIONS

Dimensions: 6.25" H x 11" W x 10" D (158mm H x 280mm W x 254mm D)

Weight: 2.75 lb (1.25 kg)

Installation: Wall/Pole Mount

Pole Mount Diameter: 2" (50mm)

Max Vertical Articulation $\pm 85^\circ$

Max Horizontal Articulation: $\pm 60^\circ$

> ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor or Outdoor

Wind Velocity: 130 mph (210 km/h)

> WARRANTY

1 Year Limited Warranty

> COMPATIBILITY

For use with the Cisco AIR-ANT2566P4W-R patch antenna.

> INCLUDED HARDWARE

Includes hardware to attach the Cisco antenna to the adapter plate, U-bolts for pole mounting and screws for wall mounting. Installer is required to provide any additional mounting/fastening hardware for other mounting situations (brick, concrete, etc.).