

Rittal – The System.

Faster – better – everywhere.

Network/server enclosures TS IT with glazed door, IP 55, with 482.6 mm (19") mounting frame – DK 5507.131

Date : Jun 6, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Network/server enclosures TS IT with glazed door, IP 55, with 482.6 mm (19") mounting frame – DK 5507.131

created: 06.06.2017 build on www.rittal.com/uk-en



Product description

Material:	Sheet steel Aluminium Glazed aluminium door with 3 mm single-pane safety glass
Surface finish:	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder-coated
Colour:	Enclosure frame and panels: RAL 7035 Interior installation: RAL 9005
Protection category IP to IEC 60 529:	IP 55 only in conjunction with baying seal or screw-fastened side panels
Supply includes:	TS 8 enclosure frame with doors and roof plate Glazed aluminium door at the front, 180° hinges Sheet steel door at the rear, 180° hinges Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E Roof plate, one-piece, solid Base tray and gland plate, multi-piece, solid Two 482.6 mm (19") mounting frames, front and rear, depth-variable Baying seal and sealing kit for gland plates (supplied loose) Connection accessories for potential equalisation with earthing point (supplied loose) 50 multi-tooth screws M5, cage nuts M5, conductive (supplied loose) IPPC pallet
Note:	Depending on how and where it is sited, the door opening angle may vary for selected applications For enclosures with height and depth 2000 x 1200 mm / 2200 x 1000 mm / 2200 x 1200 mm, the matching side panels are optionally available and are supplied fitted to the enclosure
Basic material:	Sheet steel

Product features	
Dimensions:	Width: 800 mm Height: 2000 mm Depth: 800 mm
Installation height for components:	42 U
Distance between levels as delivered:	545 mm
Load capacity:	482.6 mm (19") level: 10000 N
Packs of:	1 pc(s).
Weight/pack:	128 kg
Customs tariff number:	94032080
ETIM 6.0:	EC002499
ETIM 5.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 7.0/7.1:	27180207
eCl@ss 6.0/6.1:	27180207
eCl@ss 5.1/5.1.4:	27180201
Product description (long):	Network/server enclosure TS IT, WHD: 800x2000x800 mm, 42 U, IP 55, Glazed aluminium door at the front, Sheet steel door at the rear, 180° hinges, Comfort handle for semi-cylinders, Roof plate, one-piece, solid, Base, multi-piece, closed, without side panels, Two 482.6 mm (19") mounting frames, front and rear., Supplied loose:, 50 cage nuts and multi-tooth screws M5, potential equalisation set, Spacers to raise the fan cover plate., Surface finish:, enclosure frame, flat parts RAL 7035, Interior installation: RAL90°05.
Approvals	
Approvals:	UL + C-UL
Certificates:	Protection category