

Product data sheet

Characteristics

AR3150W

Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways.



Purchase

APC

 AR3150W

Overview

Description	Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways.
Model Name	NetShelter SX 42U 750mm Wide x 1070mm Deep Enclosure with Sides White
Includes	Baying hardware , Documentation CD , Key(s) , Keyed-alike doors and side panels , Leveling feet , Pre-installed casters , Side Panels
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Physical

Net Weight	155.63 kg
Maximum Height	1991 mm
Maximum Width	750 mm
Maximum Depth	1070 mm
Shipping Weight	167.83 kg
Shipping Height	2216 mm
Shipping Width	895 mm
Shipping Depth	1219 mm
Minimum Mounting Depth	262 mm
Maximum Mounting Depth	915 mm
Rack Height	42 U
Rack Width	482.6 MM

Color	White
Units per Pallet	1.0
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	16 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Other Environmental Compliance	China RoHS