

# Product data sheet

## Characteristics

# AR3307W

Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications.



## Purchase

APC  
 AR3307W

## Overview

Description	Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications.
Model Name	NetShelter SX 48U 600mm Wide x 1200mm Deep Enclosure with Sides White
Includes	Baying hardware , Documentation CD , Key(s) , Keyed-alike doors and side panels , Leveling feet , Mounting Hardware , Pre-installed casters , Side Panels
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

## Physical

Net Weight	138.23 kg
Maximum Height	2258 mm
Maximum Width	600 mm
Maximum Depth	1070 mm
Shipping Weight	157.35 kg
Shipping Height	2385 mm
Shipping Width	752 mm
Shipping Depth	1219 mm
Minimum Mounting Depth	191 mm
Maximum Mounting Depth	915 mm
Rack Height	48 U
Rack Width	482.6 MM

Color	White
Units per Pallet	1.0
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	18 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

### Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs