

AXIS M3007-P Network Camera

Ultra-discreet fixed mini dome with 180°/270°/360° panoramic view

The affordably priced, factory-focused AXIS M3007-P is an ultra-discreet, 5-megapixel fixed indoor mini dome that provides detailed, high quality 180°, 270° or 360° panoramic views of areas as large as 650 m² (7,000 sq ft). It offers different views: 360° overview and dewarped views such as panorama, double panorama and quad views. The quad view is suitable, for instance, when the camera is positioned at an intersection of corridors. AXIS M3007-P provides four individually cropped out and dewarped view areas where users can digitally pan, tilt and zoom in on areas of interest.

- > [Ultra-discreet design](#)
- > [360°/270°/180° panoramic views in up to 5 MP resolution](#)
- > [Digital PTZ and multi-view streaming with dewarped views](#)
- > [Edge storage with support for microSDHC card](#)



AXIS M3007-P Network Camera

Camera		Notification: email, HTTP and TCP Video recording to edge storage Pre- and post-alarm video buffering
Image sensor	1/3.2" progressive scan RGB CMOS	
Lens	M12 mount, F2.8, Fixed iris 1.3 mm Horizontal field of view: 187° Vertical field of view: 168°	
Light sensitivity	0.6–200000 lux, F2.8	
Shutter time	1/24000 s to 2 s	
Camera angle adjustment	Rotation ±180°	
Video		
Video compression	H.264 Main Profile (MPEG-4 Part 10/AVC), Motion JPEG	
Resolutions	Overview: 2592x1944 (5 MP) to 160x120 Panorama: 1920x720 to 320x120 Double Panorama: 1920x1440 to 160x120 Quad view: 1920x1440 to 160x120 View area 1–4: 1920x1440 to 160x90	
Frame rate	12 fps in 360° overview and panoramic views	
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Controllable frame rate and bandwidth VBR/MBR H.264	
Multi-view streaming	360° overview, Dewarped panorama, double panorama and quad views. Up to 4 individually cropped out and dewarped view areas. When streaming 4 dewarped view areas and one 360° overview in VGA resolution, the frame rate is 10 fps per stream	
Pan/Tilt/Zoom	Digital PTZ of view areas, Preset positions, Guard tour. Digital PT of panorama, Double panorama and quad views	
Image settings	Compression, Color, Brightness, Sharpness, Contrast, White balance, Exposure control, Backlight compensation, Wide dynamic range – dynamic contrast, Text and image overlay, Mirroring of images, Privacy mask Exposure zones, Fine-tuning of low light behavior Rotation: 0°, 180°	
Network		
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S and ONVIF Profile G, specification at www.onvif.org	
Analytics	AXIS Video Motion Detection, active tampering alarm Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap	
Event triggers	Analytics, Edge storage events	
Event actions	File upload: FTP, SFTP, HTTP, network share and email	
Data streaming	Event data	
Built-in installation aids	Pixel counter	
General		
Casing	Color: White NCS S 1002-B (for repainting instructions of skin covers, contact your Axis partner), Encapsulated electronics, Captive screws (resistor 10) Discreet, smoke-detector like design with uncovered lens, aluminum and polycarbonate/ABS casing	
Sustainability	PVC free	
Memory	512 MB RAM, 128 MB Flash	
Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 2, max 4.5 W, typical 3.4 W	
Connectors	Male RJ45 10BASE-T/100BASE-TX PoE on a 2 m (6.6 ft) network cable, warranty can be maintained even when cable is cut. For more information, contact your Axis partner.	
Storage	Support for microSD/microSDHC/microSDXC card SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Operating conditions	0 °C to 45 °C (32 °F to 113 °F) Humidity 15–85% RH (non-condensing)	
Approvals	EN 55022 Class B, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, C-tick AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24, IEC/EN/UL 60950-1	
Dimensions	Ø 131 x 53 mm (Ø 4 x 2.1 in)	
Weight	570 g (1.26 lb)	
Included accessories	Installation Guide, Windows decoder 1-user license, Drill hole template, Torx L-key	
Optional accessories	AXIS T94F01D Pendant Kit AXIS T94F02L Recessed Mount AXIS T94F01M J-Box/Gang Box Plate AXIS T94F01P Conduit Back Box AXIS T94F01S Mount Bracket	
Video management software	AXIS Companion, AXIS Camera Station and video management software from Axis' Application Development Partners (not included). For more information, see www.axis.com/vms	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	
a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (ey@cryptsoft.com).		
Environmental responsibility: www.axis.com/environmental-responsibility		