# JF Series Hands-Free Video Intercom



#### JFS-2AED

Box Set with JF-DA, JF-2MED, and PS-1820UL

Box Set with JF-DV, JF-2MED, and PS-1820UL

#### JFS-2AEDF

Box Set with JF-DVF, JF-2MED, and PS-1820UL

#### Door Stations: mix and match up to 2

(only 1 if a box set is selected – max. 1 audio door station per system)

JF-DV

Video Door Station

· Zinc die cast cover

Fixed camera

· Surface mount

→ p. 88

(included with JFS-2AEDV box set)

· Weather and vandal resistant



#### JF-DA

Video Door Station (included with JFS-2AED box set)

- Fixed camera
- · Plastic chassis
- · Weather resistant

0

· Surface mount  $\rightarrow$  p. 88

## JF-DVF-HID

Card Access Video Door Station

- HID® ProxPoint® Plus Proximity Card Reader
- · Fixed camera
- · Stainless steel panel
- · Weather and vandal resistant
- Flush mount (back box included)
- → p. 88



#### JF-DVF


Video Door Station (included with JFS-2AEDF box set)

0

- Fixed camera
- · Stainless steel panel
- · Weather and vandal resistant
- · Flush mount (back box included)
- $\rightarrow p.88$



- Plastic chassis
- Weather resistant
- · Surface mount
- $\rightarrow$  p. 87



2 wires

Aiphone

#871802

PT-1210N

12V AC Transformer

(required for EL-12S)

PS-1820UL

(included with all JFS box sets)

18V DC, 2A

Power Supply → p. 111

**Master Station** 

#### **Door Station Features**


- Fixed camera provides clear visitor identification (video door stations)
- · Card access door station available


#### **Master Station Features**

- Compact, attractive design complements most interiors
- · Hands-free or push-to-talk communication
- Leave up to 3 voice memos to be heard at the master station (approx. 15 seconds per memo)
- Pre-record up to 2 entrance messages to manually control from the master station, but to be heard at the door station (approx. 10 seconds per message)
- Single or selective door release with RY-3DL
- · Video monitoring
- Picture memory records up to 50 calls (JF-2MED only)
- · All Call to inside master and sub stations
- · Video out to DVR via supplied connector

#### **System Features**

- Convenient box sets are complete with a master station, each with a different door station, and a power supply (1 more door station and up to 2 sub master stations can be added for a full 2 x 3 system)
- Quick and easy to install only 2 wires!
- Expandable to three inside and two door stations
- All video master station screens turn on when door station calls in





## JF Series Components (continued)

#### **Video Door Stations**



#### JF-DA

Video Door Station (included with JFS-2AED box set)

- · Fixed camera
- Plastic chassis
- · Weather resistant
- Surface mount



- · Fixed camera
- · Zinc die cast cover
- · Weather and vandal resistant
- · Surface mount



#### JF-DVF

Video Door Station (included with JFS-2AEDF box set)

- · Fixed camera
- · Stainless steel panel
- · Weather and vandal resistant
- · Flush mount (back box included)



### JF-DVF-HID\*

Card Access Video Door Station

- HID® ProxPoint® Plus Proximity Card Reader
- · Fixed camera
- Stainless steel panel
- · Weather and vandal resistant
- · Flush mount (back box included)



available for flush mount stations! See p. 106

\* HID® stations require a 3rd party host. Power for card reader and door strike require additional wire.

#### **Features**

· Fixed camera provides clear video

 LED illumination automatically turns on in low light conditions

#### **Features**

(additional for JF-DA)

- · Locator LED above call button
- · Mounts directly to wall or 1-gang box

#### Features (additional for JF-DV, JF-DVF, JF-DVF-HID)

· LED backlit nameplate

#### **Specifications**

Power Source Supplied by Master Station

Communication Hands-free

Camera Type: 1/4" CCD

Area View: 2'1" vert. x 3'1" horiz. at 20"

Temp. Rating 14°~140°F (-10°~60°C) Material JF-DA: fire resistant PC + ABS plastic

JF-DV: zinc die cast

JF-DVF JF-DVF-HID:

stainless steel

Mounting JF-DA: surface mount directly to wall or 1-gang box

> JF-DV: surface mount directly to wall

JF-DVF: flush mount with included back box or surface mount with SBX-DVF

JF-DVF-HID: flush mount with included back box or surface mount with SBX-DVF-P

Wire Type Door Station to Master Station:

2-cond., low cap, non-shielded – use Aiphone #871802


Distance Door Station to Master Station: 165'(22AWG) 330'(18AWG)

ė






#### JF-DVF



#### JF-DVF-HID



### **Long Distance Adaptor**



## JBW-BA

Long Distance Adaptor for Video **Door Stations** 

#### **Features**

- · Extends wiring distance from door stations to master stations up to 820' max.
- · Requires low capacitance Aiphone wire #851602 or #851602DB

#### **Specifications**

Power Source 18V DC - use PS-1820UL

One adaptor unit for each Capacity

video door station located beyond the standard specified wire distance

Mounting DIN rail (included)

Wire Type 2-cond., low cap, PE, use Aiphone #851602 or #851602DB (direct burial)

Distance Adaptor to Door Station: 820'

Adaptor to Master Station: 165'



4-13/16"

2-3/8"