



Model 600S

600 lbs Single Magnetic Lock

Specifications

- 600 lbs holding force
- Magnet size: 9-7/8" L x 1-11/16" H x 1" W
- Armature size: 7-1/4" L x 1-7/16" H x 5/8" W
- Operates on 12 or 24 VDC, selectable
- Low current draw: 400 mA at 12 VDC, 200 mA at 24 VDC
- Operating Temperature: +14 to +131F [-10 to +55C]

Features

- Instant release, no hysteresis
- Non-aluminum parts are plated to resist corrosion
- Built-in arc suppression
- Can be used with any access control system
- E-Z mount system, no special tools required
- Self drilling TEC screws

Options

- Clear anodized (US28) finish standard
- Duranodic (US40) finish available
- Dress covers in polished chrome and brass are available

Certifications & Listings

- UL 10C fire rated
- CAN4-S104 (ULC-S104) fire door conformant
- ULC-S527 listed
- UL 864 listed

Models

600S

600 lbs Single Door Magnetic Lock, 12 or 24 VDC, UL 10C and Canadian UL Listed

600SDURO

600 lbs Single Door Magnetic Lock, 12 or 24 VDC, US 40 Duranodic Finish, UL 10C and Canadian UL Listed

ALARMCONTROLS



ASSA ABLOY