

AR203A

NetShelter 4 Post Open Frame Rack 44U Square Holes



Overview

Model Name	NetShelter 4 Post Open Frame Rack 44U Square Holes
Includes	Installation guide
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO , THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , <![CDATA[Cote D'Ivoire]]> , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova , Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	88.9 lbs (40.41 kg) (40.41 kg)
Maximum Height	83.86 inches (2130.0 mm) (2130.0 mm)
Maximum Width	23.62 inches (600.0 mm)
Maximum Depth	29.41 inches (747.0 mm) (747.0 mm)
Shipping Weight	90.0 lbs (40.82 kg) (40.82 kg)
Shipping Height	82.0 inches (2083.0 mm) (2083.0 mm)
Shipping Width	10.0 inches (254.0 mm) (254.0 mm)
Shipping Depth	4.43 inches (113.0 mm) (113.0 mm)
Minimum Mounting Depth	29.13
Maximum Mounting Depth	29.13
Rack Height	44 U
Color	Black
Units per Pallet	0.0
Vertical Posts	0 gauge
Front Door	0 gauge
Rear Door	0 gauge
Roof	0 gauge
EIA Mounting Rails	0 gauge
Side Panels	0 gauge

Environmental

CFM	0
-----	---

Conformance

Standard warranty	5 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs