



Purchase

APC
 AP9551

Overview

Model Name	Rack PDU, Basic, Zero U, 20A, 120V, (14)5-15
Includes	Rack Mounting brackets , Toolless Mounting Kit , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Netherlands Antilles , Aruba , Barbados , Bermuda , Brazil , Bahamas , Canada , Colombia , Costa Rica , Dominica , Dominican Republic , Ecuador , Grenada , Guadeloupe , Guatemala , Honduras , Haiti , Jamaica , SAINT KITTs AND NEVIS , Martinique , Mexico , Nicaragua , Panama , Puerto Rico , El Salvador , Turks And Caicos Islands , Trinidad And Tobago , Taiwan , United States , SAINT VINCENT AND THE GRENADINES , Venezuela

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	20 A
Output Connections	(14) NEMA 5-15R (Battery Backup)
Overload Protection	Yes

Input

Nominal Input Voltage	100V , 120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	16 A
Input Connections	NEMA L5-20P
Cord Length	3.66 meters
Number of Power Cords	1
Acceptable Input Voltage	90-132 VAC
Maximum Line Current per phase	20 A
Maximum Input Current per phase	20 A

Load Capacity	2400 VA
---------------	---------

Physical

Net Weight	2.21 kg
Maximum Height	610 mm
Maximum Width	42 mm
Maximum Depth	44 mm
Shipping Weight	2.92 kg
Shipping Height	648 mm
Shipping Width	178 mm
Shipping Depth	152 mm
Color	Black

Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CUL Listed , CSA , UL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------