

AR7588

The vertical channels have smooth plastic fingers at 1U increments to allow patch cords to enter and exit in an organized manner.



Overview

Description	The vertical channels have smooth plastic fingers at 1U increments to allow patch cords to enter and exit in an organized manner.
Model Name	Vertical Cable Manager for NetShelter SX 750mm Wide 48U (Qty 2)
Includes	Installation guide , Mounting Hardware , Qty 6 - Cable retainers with snap hinges
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , <![CDATA[Cote D'Ivoire]]> , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Supported Hardware

Panel Size	0
Brightness	0 nits

Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	5.27 kg
Maximum Height	2184.0 mm
Maximum Width	97.0 mm
Maximum Depth	160.0 mm
Shipping Weight	5.73 kg
Shipping Height	203.0 mm
Shipping Width	165.0 mm
Shipping Depth	1092.0 mm
Minimum Mounting Depth	0.0
Maximum Mounting Depth	0.0
Rack Height	0 U
Color	Black
Units per Pallet	0.0
Vertical Posts	0 gauge
Front Door	0 gauge
Rear Door	0 gauge
Roof	0 gauge
EIA Mounting Rails	0 gauge
Side Panels	0 gauge

Environmental

CFM	0
-----	---

Conformance

Approvals	TAA compliance
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs