

A0407001 Modular Connectors - MDVO insert 1-Port F Connector



For more Information
please call

1-800-Belden1

General Description:

MDVO insert 1-Port F Connector

Usage (Overall)

Suitable Applications:	Audio and Video applications
Related Parts:	- Compatible MDVO Faceplate and Patch Panel

Physical Characteristics (Connectivity)

Access

Dimensions

Dimensions:

Height (mm)	Width (mm)	Depth (mm)
16.002	16.002	28.956

Materials

Materials:

Description	Type	Material
Front Connection	F	Metal
Rear Connection	F	Metal
Insert		Plastic - UL940V-0

Color

Color:	White
--------	-------

Weight

Weight:	0.005 kg
---------	----------

Packaging

Packaging:	10 units packaged in a plastic bag.
------------	-------------------------------------

Mechanical Characteristics (Connectivity)

Footprint/Type:	MDVO-Style
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

Safety Listing:	Bi-national Standard Listed
-----------------	-----------------------------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product, visit our web site at <http://www.belden.com>.

Notes (Cont'd.): Thread pitch: 3/8-32 UNEF, Overall length: 27mm, Beryllium insert, DC - 3GHz sweep.

Product Family

Part Number List:

Item Number	Color
A0406999	Gray
A0407000	Almond
A0407001	White
A0407002	Black
AX102599	Ivory

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0407001	1 EA	0.021 LB			MDVO VIDEO F COAXIAL

A0407001 Modular Connectors - MDVO insert 1-Port F Connector

Revision Number: 0 Revision Date: 02-19-2015

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.