# **B10 Medium Control Panel Enclosure**

www.boschsecurity.com





- ► Easy-to-install standoff location for mounting supported modules
- ▶ Made with cold-rolled steel with a white semi-gloss
- ▶ Easy access locations for battery placement
- ▶ Optional tamper switch mounting location

The B10 is a white enclosure made of cold-rolled steel that is 1.0 mm (20 gauge) thick. It is compatible with the following peripherals:

- D101 Lock and Key Set. Standard lock set with one key supplied. Uses the D102 (#1358) replacement key. Order number D101.
- D110 Tamper Switch. Screw-on tamper switch that fits all enclosures. Shipped in packages of two. Order number D110.
- ICP-EZTS Dual Tamper Switch. Combination tamper switch with a wire loop for additional tamper outputs. Order number ICP-EZTS.

#### Certifications and approvals

Region	Certification		
USA	CSFM	see our website	

## **Parts included**

Quantity	Component
1	Enclosure
1	Hardware pack
1	Installation Manual

#### **Technical specifications**

#### **Properties**

Dimensions	37 cm x 32 cm x 8.9 cm (14.5 in x 12.5 in x 3.5 in)
Weight	3 kg (6.7 lb.)
Material	1.0 mm (20 gauge) cold-rolled steel
Color	White

#### **Environmental considerations**

Mounting considerations N	Mount in dry indoor locations.
---------------------------	--------------------------------

## **Ordering information**

## **B10 Medium Control Panel Enclosure**

White, steel enclosure. Accepts an optional lock and tamper switch. Measures 35.6 cm x 31.8 cm x 7.6 cm (14 in x 12.5 in x 3 in).

Order number B10