

CompuLink fiber optic patch cord

LC (ceramic) to LC (ceramic) ultra polish, 2-fiber yellow jacketed 8.3/125 OS2 riser rated zipcord.

- * Premium performance, exceeds EIA/TIA-568 specifications with maximum insertion loss of less than 0.55 dB.
- * End—face geometry and internal processes are validated through interferometer testing.
- * Built using Corning connectors and cordage.
- * Individually bagged.

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

REV	DESCRIPTION	DATE	BY

ANIXTER PART No.	VENDOR PART No.	LENGTH FT.	LENGTH MT.
246866	LCCLCCD1-UPSM	3.3 FT.	1 MT.
246867	LCCLCCD2-UPSM	6.6 FT.	2 MT.
246868	LCCLCCD3-UPSM	10.0 FT.	3 MT.
357440	LCCLCCD4-UPSM	13.1 FT.	4 MT.
246869	LCCLCCD5-UPSM	16.4 FT.	5 MT.
266848	LCCLCCD7-UPSM	23.0 FT.	7 MT.
266870	LCCLCCD10-UPSM	32.8 FT.	10 MT.
255835	LCCLCCD15-UPSM	49.2 FT.	15 MT.

DRAWN:	G.KRUG	DATE	2/27/12
CHECKED:		DATE	
AP	PROVALS		DATE
ENGINEER	NG:		
QUALITY:			



CADD REF. No.: LCLCOS2RISER DRAWING NO. LC-LC-OS2-RISER

FORM: MASTER 8/22/00