Product Specifications





760109736 | M4800A-1U-PS

M4800A 1U Angled Panel, 48 port, for SYSTIMAX Category 5E Information Outlets and Uniprise Category 6 and 5E Information Outlets

Available for use with the DYMO® labeling solution

Dimensions

Depth 143.00 mm | 5.63 in Height 44.45 mm | 1.75 in Width 482.60 mm | 19.00 in

Electrical Specifications

ANSI/TIA Category 3 | 5e

Environmental Specifications

Flammability Rating UL 94 V-0

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Relative Humidity Up to 95%, non-condensing

Safety Standard CUL | UL

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type Passive

Product Type Panel, modular Brand CommScope®

Color Black Package Quantity 1

Rack Type EIA 19 in

Rack Units 1

Mechanical Specifications

Panel Style Angled

Material Type High-impact, flame retardant, thermoplastic | Steel

Regulatory Compliance/Certifications

AgencyRoHS 2011/65/EU

Classification
Compliant

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

