



Powering Business Worldwide

pe.eaton.com

5PX Rack/Tower UPS

5PX2200RTN

UPC:743172039484

Dimensions:

- **Height:** 7.5 IN
- **Length:** 10.2 IN
- **Width:** 3.4 IN

Weight:13.1 LB

Notes:NETWORK MS CARD IS NOT INSTALLED.
Allows start of UPS without utility power.

Warranties:

- 3 year on electronics, 3 year on batteries with registration

Specifications:

- **Special Features:** ABM technology and temperature-compensated charging method (user selectable), automatic battery test, deep discharge protection, automatic recognition of EBMs.
- **Accessories:** Tower pedestals, Phillips head screw driver
- **Battery Type:** VRLA, Hot-swappable internal batteries
- **Frequency Rating:** 40-60 Hz
- **Humidity:** 0-90% non-condensing
- **Input:** (1) IEC-320-C14
- **Operating Temperature:** 0° to 40°C
- **Output:** (8) 5-20R
- **Output Voltage:** 230V
- **Topology:** Line interactive
- **User Interface:** LCD graphical display
- **Volt Ampere Rating:** 700 KVA
- **Battery Rating:** 12V/9 Ah
- **Cable Type:** RS-232 serial cable, USB cable
- **Cord Length:** 96 FT



- **Indicator:** Load protected (LED), battery and fault (LED)
- **Mounting Hardware:** Four-post rail kit
- **Serial Interface:** Network Card-MS
- **Software:** Intelligent Power Software Suite CD, User manual CD
- **Voltage Rating:** 89-151V (adj to 70-153V)
- **Wattage:** 420W
- **Color:** Black
- **Communication:** RS-232 serial port , plus contact closures

Supporting documents:

- [Eaton 5PX UPS](#)
- [Product and Service Catalog](#)
- [Product Data Sheet - 5PX2200RTN](#)

Certifications:

- cTUVus
- UL 497A
- UL 1778
- NOM

Product compliance:

- CE Marked