



Powering Business Worldwide

pe.eaton.com

9130 Tower UPS

PW9130L1000T-XL

UPC:790341052720

Dimensions:

- **Height:** 9.1 IN
- **Length:** 15.1 IN
- **Width:** 6.3 IN

Weight:30.9 LB

Notes:Thermal protection switches load to bypass in case of overheating, Allows UPS operation without utility input

Warranties:

- 2 year limited factory

Specifications:

- **Accessories:** User Guide, Quick Start Instructions, Cord-Retention Brackets
- **Battery Type:** 36 Vdc, Hot-swappable internal batteries, EBM
- **Efficiency:** >95% in high-efficiency mode, >86% in online mode
- **Frequency Rating:** 50-60 Hz
- **Humidity:** 5-90% non-condensing
- **Input:** (1) 5-15P
- **Operating Temperature:** 0° to 40°C
- **Topology:** Online Double Conversion
- **User Interface:** Graphical LCD with blue backlight and text in English, French, German, Russian and Spanish
- **Volt Ampere Rating:** 1000 KVA
- **Cable Type:** USB Cable
- **Color:** Black
- **Cord Length:** 864 IN
- **Runtime:** 10 min full load, 24 min half load
- **Wattage:** 900W
- **Battery Rating:** (3) 12V, 9 Ah



- **Configuration:** Tower
- **Nominal Ac Current:** 8.3A
- **Serial Interface:** RS-232, USB
- **Software:** Intelligent Power Software Suite

Supporting documents:

- [Product and Service Catalog](#)
- [Product Data Sheet - PW9130L1000T-XL](#)

Certifications:

- EN 55022
- cUL Listed
- UL Listed
- VCCI

Product compliance:

- FCC Class B