



The 1006 Series is also available in a **Complete One Box** Solution

Shown with KM Option

The 1006 series is the strongest and most versatile electric strike available. The dual interlocking plunger design and heavy duty stainless steel construction, enables it to exceed every standard developed for electric strikes. With multiple faceplate options, the 1006 will fully accommodate every lock designed to work within an ANSI 4-7/8" strike plate. Tested to exceed 3,000 lbs. of static strength, 350 ft-lbs. of dynamic strength and factory tested to exceed 1,000,000 cycles of operation, the 1006 is in a class of its own.



1006 Series

The strongest, most versatile electric strike available

Specifications

- UL 10C fire-rated, 3 hour single door (fail secure only)
- UL 10C fire-rated, 1-1/2 hour double door (fail secure only)
- CAN4-S104(ULC-S104) fire door conformant
- ANSI A250.13-2003 windstorm listed
- UL 1034, burglaryresistant listed and suitable for outdoor use
- UL 294 (6th Edition) listed
- ANSI/BHMA A156.31, Grade 1
- NFPA-252 fire door conformant

- ASTM-E152 fire door conformant
- MEA New York City accepted
- Florida Building Code approved FL#4776
- RoHS compliant
- Environmental **Product Declaration**
- Patents: 6,021,038 & 6,595,564

Frame Application


- Metal
- Wood


Electrical (continuous duty)

- .45 Amps at 12 VDC
- .25 Amps at 24 VDC

1006 Models

TOOUTVIOUCIS		
1006	Universal electric strike	Faceplate options ordered separately, see pages 12-16
1006CS	Complete electric strike	Includes the SMART Pac II and J, KD, KM, HM, and AD faceplates
1006CLB	Complete electric strike	Includes the J, K, KD, and KM faceplates
1006CDB	Complete electric strike	Includes the HM and AD faceplates
RF1016	Integrated Prox	Includes the strike body, Prox reader and door position switch
IC1026	Integrated iCLASS®	Includes the strike body, iCLASS reader and door position switch





Standard Features

- Stainless steel construction
- Tamper-resistant
- Static strength 3,070 lbs. (fail secure)
- Dynamic strength 350 ft-lbs. (fail secure)
- Endurance 1,000,000 cycles
- Fail secure
- Dual-voltage 12 VDC or 24 VDC continuous duty
- Non-handed
- Internally mounted solenoid
- Accommodates up to 1" deadbolt
- · Plug-in connector
- Full keeper shims for horizontal adjustment
- Trim enhancer
- Five-year limited warranty

Optional Features

LBM » Latchbolt monitor
LBSM » Latchbolt strike monitor

• Fail safe

Interchangeable faceplates
 Monitor Switches may not work with all faceplate options (see pages 12-16)

Accessories

1000-102 » Rain guard

1006-103 » Full keeper shims

1000-104 » Lip extension trim adapter

1006-105 » Trim enhancer BLK (goof plate)

1006-109 » Trim adapter

1000-110 » Replacement strike plate

1000-130 » KD filler plate

150 » Strike latch guard

154-MTK » Metal template kit

2004M » ElectroLynx® adapter

2005M3 » SMART Pac® III

2006M » Plug-in buzzer

Finishes

630 » Satin stainless steel

605 » Bright brass

606 » Satin brass

612 » Satin bronze

613 » Bronze toned

629 » Bright stainless steel

BLK » Black

*Complete Pacs are only available in the 630 finish



























