

12VDC Power Supplies & Accessories

12VDC1AMP 1 Amp 12 Volt DC Power Supply



FEATURES

- ◆ 1 Amp Output
- ◆ Class II Transformer
- ◆ UL/CUL Listed

12VDC2AMP 2 Amp 12 Volt DC Power Supply



FEATURES

- ◆ 2 Amp Output
- ◆ Class 2 Transformer
- ◆ UL/CUL Listed

SPECIFICATION	12VDC1AMP	12VDC2AMP
Type	Class II, UL/CUL Listed	Class II, UL/CUL Listed
Input	AC 100-240V 50/60HZ 0.35A MAX	AC 100-240V 50/60HZ 0.35A MAX
Output	12 Volt DC 1 Amp (Regulated)	12 Volt DC 2 Amp (Regulated)
Misc.	Center Pin Positive	Center Pin Positive

PSMINI4C5AUL 4 Channel 5 Amp 12 Volt DC Power Supply



Power Output



Power Input



FEATURES

- ◆ UL / CUL Listed
- ◆ Built in PTC Fuse for Protection
- ◆ Adjustable Output Voltage up to 13.8V
- ◆ 100V-240V Wide Range Input Voltage
- ◆ Led Indicator Light
- ◆ Sliding Terminal Strip Cover
- ◆ Power Cord Included

SPECIFICATION	PSMINI4C5AUL
Number of Outputs	4
Input Voltage	AC 100V-240V
Adjustable Output Voltage	12 ~ 13.8 Volt DC
Output Current	5 Amp
Fuse Type	PTC 6 Amp
LED Indicator	Yes
Certificates	UL / CUL
Operating Temperature	-22°F ~ 113°F
Weatherproof Rating	Indoor Only
Dimensions (H x W x D)	6.5" x 2.12" x 1.37"