

Security Rated LED Monitors: 17" & 19"

HDMI, VGA & BNC Video Inputs, PC Audio In/Output



| SPECIFICATION | LED17ST | LED19ST |
|-----------------------------------|--|------------------------|
| Video System | NTSC/PAL (Auto Sensing) | |
| Max Resolution | 1280 x 1024 (Native) | |
| Supported Resolutions | 720x400; 640x480; 800x600; 1024x768; 1280x1024; 1920x1080 (Upscaled) | |
| Video Connections | HDMI, VGA, BNC 1 Input, BNC 2 Input/Output | |
| 3D Comb Filter | Yes | |
| 3D De-Interlace | Yes | |
| OSD (On Screen Display) | Yes | |
| Backlight | LED | |
| Active Display Area | 17" Diagonal | 19" Diagonal |
| Impedance | 75 OHM Self Terminating | |
| Video Input Signals | HDMI, VGA, Composite BNC | |
| Aspect Ratio | 5:4 | |
| Pixel Pitch | 0.264 | |
| Color Depth | 24 bits, 16.7 Million colors | |
| Brightness | 220 cd/m ² | 250 cd/m ² |
| Contrast Ratio | 1000:1 | |
| Viewing Angle (H/V) | 170°/160° | 178°/178° |
| Response Time | 5ms | |
| Auto Adjustment | Yes | |
| Certificates | CE, FCC, UL | |
| Languages | English, Chinese, German, French, Spanish, Italian | |
| Input Voltage | 12VDC UL/CUL External Power Supply Included | |
| Power Consumption | <25W | |
| Audio Connections | PC Audio (3.5mm Stereo) for VGA & BNC Input | |
| Speakers | 8Ω, 2 Watt per Channel | 8Ω, 3 Watt per Channel |
| Dimensions with stand (H x W x D) | 14.6" x 15.2" x 7.2" | 16.2" x 16.5" x 7.2" |
| Weight | 9.8lb | 10.5lb |
| Vesa Mounting | Yes (100 x 100) | |
| Operating Temperature | 32° ~ 104°(0°C ~ 40°C) | |

Note: Specification subject to change without notice

FEATURES

- ◆ LED Backlight
- ◆ Low Power Consumption
- ◆ Includes 6' HDMI & VGA Cables
- ◆ Up to 1280 x 1024 Resolution
- ◆ 3D Comb Filter
- ◆ 3D De-Interlace
- ◆ 3D Digital Noise Reduction
- ◆ Super Fast 5ms Response Time
- ◆ HDMI & VGA Inputs
- ◆ Looping BNC Input
- ◆ PC Audio Input/Output
- ◆ Full OSD Control of All Monitor Functions
- ◆ 5:4 Aspect Ratio
- ◆ Vesa Mounting (100 x 100)
- ◆ CE, FCC, UL Certifications

INCLUDED ACCESSORIES

1. 6' HDMI Cable
1. 6' VGA Cable
1. 3.5mm PC Audio Cable
1. Power Cord / Power Supply
1. User Manual

REAR PANEL CONNECTIONS

