

SELECTIVE CALL INTERCOM 8-LOCATION DISTRIBUTION MODULE

IC5001 | [On-Q](#)



FEATURES & BENEFITS

This selective call module supports up to eight selective call room, door or patio units, with the ability to cascade up to four modules for up to 32 units. It also allows integration with the lyriQ Audio System to support audio interrupt during an intercom page.

DISCONTINUED. Superceded by IC5010.

- Cascade up to 4 modules for 32 total units.
- Easily integrates with lyriQ Audio System to support audio interrupt.
- Supports door release.
- Assignable LCD trigger for camera monitoring of door.
- Power supply not included. Recommend PW1030 .
- Supports up to eight selective call units.
- Includes 20 door tones.

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes
Superceded By: IC5010

CONSTRUCTION INFORMATION

Spec 1: Power Requirements

DIMENSIONS

Overall Dimensions (US): 3" H x 4.5" W x 1.65" D
Product Weight (US): 2 lb

TECHNICAL INFORMATION

Cat5 Cable Rating: CAT5 UTP, 4 pair solid conductor (24 AWG)
Humidity: Up to 90% RH (non-condensing)
Material: Subplate Material - ABS Plastic
Operating Temperature (Celsius): 0 to 55°C
Power Requirements: +24Vdc, +/-1.5Vdc, 2.5 A max

QLink Selective Call Ports: RJ-45
Storage Temperature: -25 to 75°C