

---

## IN-WALL AMPLIFIER

NV-WA40W-DC | [Nuvo](#)



---

### FEATURES & BENEFITS

Nuvo's WA40 equips classrooms and other environments with a simple-to-use amplification option, designed for ample power and crisp audio reproduction.

- 40 watt amplifier, perfect for delivering audio to any enclosed listening setting
- ENERGY STAR qualified
- Easy four-button control from both amplifier and portable IR controller
- Both hard-wired rear source inputs and front-end source inputs for flexibility in using multiple devices with the system
- Speakers included for a simple, all-inclusive approach to classroom amplification

---

### SPECIFICATIONS

#### DIMENSIONS

Overall Dimensions (Metric): 5cm H x 5cm W x 2.9cm D

Overall Dimensions (US): 1.97" H x 1.97" W x 1.14" D

Primary Packaging Weight (Metric): 7kg

Product Weight (Metric): .11kg

Product Weight (US): .24lbs

#### TECHNICAL INFORMATION

Frequency Response: 20-20kHz  $\pm$ 2 dB

Output Impedance: 4 ohms

Power Peak: 45W

Power Requirements: 16VDC