



























INDOOR CONTROL PANELS & PANEL OPTIONS

INDOOR CONTROL PANELS & PANEL OPTIONS					
Part Number	W PANELS		W PANEL OPTIONS	XT PANELS	
	WIP620	WIP630	WWB100	XT-IP620	XT-IP630
			 WiFi Board		
Description	Ethernet-only W Panel	Ethernet+Cell W Panel	WIO100 	Ethernet-only XT Panel	Ethernet+Cell XT Panel
Applications	Standalone or upgrade capability. In upgrade mode, the panel, using WIO100 option, will piggyback onto a third party burglar alarm system. Compatible with VideoApp4All smartphone app, WIO100 (Input/Output Board), WWB100 (WiFi Board), and WIS100 (wired Indoor Siren).		Input/Output Board 1 Programmable/Arming input 2 Programmable outputs	Standalone or Xtender capabilities. In Xtender mode, the panel can be added as Cellular/IP backup/takeover to third-party burglar alarm systems. Inputs can be mapped to initiate MotionViewer videos. Compatible with VideoApp4All smartphone app.	
Outputs	2 Programmable outputs with WIO100		WIS100	2 Programmable outputs (included)	
Alarm Inputs	1 Programmable/Arming input with WIO100			2 Arming inputs (included), 3 Programmable inputs (included)	
Zones	24		Indoor Siren	24	
Temp Rating	Standard (14 to 104 °F)		Must be wired to W Panel (whether mounted beside or separated). Use SE601 if wireless siren is needed for application.	Standard (14 to 104 °F)	
Communication	IP Ethernet, WiFi with WWB100	IP Ethernet, Cellular, WiFi with WWB100		IP Ethernet	IP Ethernet, Cellular
Power Options	PP5			PP4	PP1 or PP4

	OUTDOOR CONTROL PANEL		POWER OPTIONS		
Part Number	XTO-IP630		PP1	PP4	PP5
					
Description	XT-IP630 control panel with a protective NEMA enclosure and internal high gain cellular and RF antennas. Ideal for outdoor and cold/hot weather installations where the panel needs protection from the elements, extreme temperatures or the greatest RF range.		4 D-Cell Lithium Batteries. Compatible with all XT Panels	12V DC Power Adapter. Compatible with all XT Panels	12V DC Power Adapter. Compatible only with W Panels
Features	Outputs: 2 Programmable Alarm Inputs: 2 Arming, 3 Programmable Zones: 24 Power Options: PP1 or PP4	Communications: IP Ethernet, Cellular Temperature Rating: -20 to 140 °F	High Activity: 1-2 years life Low Activity: 3-4 years life	Includes 3-6 months battery backup.	Includes rechargeable battery backup.

	MOTIONVIEWERS®		ACCESSORIES	
Part Number	IMV601	DCV651	MB110	MB120
				
Description	Indoor MotionViewer®	Outdoor MotionViewer®	Mounting Bracket	Magnetic Base
Application	Indoor PIR with integrated digital day/night camera. Takes a 7 second video clip upon PIR violation. Includes built-in infrared illumination up to 23 feet and variable sensitivity settings.	Outdoor PIR with integrated digital camera. Takes a 7 second video clip upon PIR violation. Includes built-in infrared illumination up to 30 feet and variable sensitivity settings.	Outdoor mounting Bracket attaches to the DCV651 Outdoor MotionViewer.	Optional magnetic base add-on to the MB110 mounting bracket.
Outdoor Capable	No	Yes - Extreme Temp (-20 to 140 °F) and IP65 outdoor-rated	Yes	

	ARMING DEVICES			
Part Number	XMA621	WMB621	RC601	BR651
				
Description	Vertical Alpha Keypad	Horizontal Alpha Keypad with Prox Tag Reader	Portable Remote Control	Prox Tag Arming Station
Application	Wireless keypad with LCD display. A keypad is required for initial programming and general maintenance. Can be used for arming and disarming.	Wireless keypad with integrated prox tag reader and LCD display. A keypad is required for initial programming and general maintenance. Compatible with VT100 prox tags.	Wireless remote control for arming/disarming. Portable device and includes 4 buttons for special arming modes and panic.	Wireless outdoor prox tag reader for arming / disarming. Blinking LEDs display armed/disarmed status. Compatible with VT100 prox tags (pictured). Temp rated -20 to 140 °F

	ADDITIONAL PERIPHERAL DEVICES				
Part Number	SE601	OSX601	IDC601	CT601	IMD601
					
Description	Indoor Siren	Outdoor Siren	Door / Window Contact	Door / Window Contact	Motion Sensor
Application	Wireless device adds 115 dB siren to system. Sounds door chime, entry and exit delays at low volume, and intrusion.	Wireless outdoor siren. 115dB sounder activates on intrusion only and includes flashing LED strobe. Temp rated -20 to 140 °F	Wireless device ideal for stay-at-home mode.	Wireless device ideal for stay-at-home mode. Includes terminals.	Wireless sensor ideal for installs where client prefers no camera.