

10-WAY IDC TELEPHONE MODULE WITH RJ31X

TM1110 | [On-Q](#)



FEATURES & BENEFITS

This telephone module distributes up to 4 incoming telephone lines (110 IDC Punchdown) to 10 locations.

- Supports up to 10 locations
- Includes RJ31X line seizure port for security installations
- Mounting bracket included
- UL listed

SPECIFICATIONS

GENERAL INFO

Color: Black
 Connection Type: Phosphor Bronze contacts, plated Gold over Nickel
 Type: Telecom Module
 Input Plug Type: RJ45 Male

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
 UL Standard: Yes
 UN SPSC: 43222819

DIMENSIONS

Height (Metric): 7.9 cm
 Height (US): 3.1"
 Length (Metric): 4.1 cm
 Length (US): 1.6"
 Width (Metric): 14.7 cm
 Width (US): 5.78 in
 Product Weight (US): 1.05 pounds

TECHNICAL INFORMATION

Connection Method: RJ45, RJ31X
 Material: 18 Gauge Cold Rolled Steel
 Mounting: Enclosure

Receptacle Type: 1x RJ31x, 11x 110 IDC Telecom
Number Of Receptacles: 12