
IN-WALL SPEAKER VOLUME CONTROL

AU0100-WHLA-V1 | [On-Q](#)



FEATURES & BENEFITS

Allows control of speaker volume at the wall. Both white and light almond color options included in packaging.

- Rated at 100 watts per channel
- Built-in impedance matching for easy installation
- Smooth turning rotary knob
- Wall plate included
- Also includes pieces to convert to a light almond finish

SPECIFICATIONS

GENERAL INFO

Cable Type: Speaker Wire

Color: White/Light Almond

Connection Type: Terminal Block

Type: Audio Speaker Volume Control

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

CONSTRUCTION INFORMATION

Installation Location: In-Wall

DIMENSIONS

Depth (Metric): 8.3 cm

Depth (US): 3.25"

Height (Metric): 10.6 cm

Height (US): 4.19"

Width (Metric): 4.2 cm

Width (US): 1.65 in

TECHNICAL INFORMATION

Material: High Impact Plastic

Mounting: Single Gang Electrical Box