

Professional Video Surveillance Monitors



Specifications

Model	TME43
Size	42.51" diagonal
Aspect Ratio	16:9
Back-light	LED
Resolution	1920 x 1080p
Brightness	330 nits
Contrast Ratio	1200:1
Response Time	8ms
Inputs	DVI via adapter through HDMI (DVI to HDMI adapter is not included) BNC In x 1 (via adapter, included) HDMI x 2, AV In x 2, PC Audio x 1 VGA x 1, Component Video - YPbPr and Built-In Speaker, USB x 2
Outputs	BNC Out x 1 (via adapter, included), Audio Out (L+R) x 1
Speaker Output	8 x 2 watts
Viewing Angle	176 (H) x 176 (V)
Power Consumption	<75 watts
Power Voltage	AC 120-240V
Product Dimensions W/D/H without Base	38.11" x 3.03" x 22.24"
Product Dimension W/D/H with Base	38.11" x 3.03" x 24.25"
Base Dimensions	24.48" x 8.81 x 2.14"
Packaging Dimensions	42.71 x 26.25 x 5.90
VESA Mounting & Wall Mount Option	200mm (H) x 300mm (V) compatible with TWM-3255 Wall Mount
Weight with Base	Net: 17.63 lbs, Gross: 22 lbs
Warranty	3 Years Limited

Specifications subject to change without notice. Doc#0802.16

www.tatungusa.com