

uplink® 4640G



Uplink Advantages

Secure dealer website for activation, configuration, and management

Flat-rate billing with no overage charges

Programmable periodic test intervals

Works with virtually any central station

Uplink Remote for interactive control and end-user notifications

Live technical and activation support*

*8:00 a.m. to 8:00 p.m. EST, Monday through Friday
Specifications subject to change without notice.

Interactive GSM Alarm Communicator

The Uplink 4640G provides a single cellular interface for four major alarm panel brands. The 4640G also transmits real-time alarm events and allows dealers to remotely configure and manage the alarm panel. In addition the 4640G supports Uplink Remote™ to provide remote arming and disarming of alarm systems from any internet enabled computer, tablet, or smart phone.

Uplink 4640G Programming Features:

- ✓ Switch selectable alarm panel interface for:
 - Honeywell Vista
 - DSC PowerSeries
 - Interlogix NetworX
 - Interlogix Concord 4
- ✓ View panel and zone status
- ✓ Arm away or stay, and disarm panel remotely
- ✓ Modify, add, and remove access codes
- ✓ Access history log
- ✓ Installs in minutes with complete end-to-end signal verification

Canadian Model # 4640G CN

(888) 9-UPLINK | (888) 987-5465 | www.uplink.com | sales@uplink.com

A **Numerex** Solution



4640G Interactive GSM Alarm Communicator



A Trusted Partner

Uplink, a Numerex Solution, is the security industry's most trusted source for wireless alarm communicators.

Uplink delivers the unique combination of technology, quality, options, and superior value that have made us the industry's trusted source for security solutions since 1996.

With hundreds of thousands of installed devices throughout the United States, Mexico, and Canada, Uplink has the experience and expertise to provide reliable, award winning products with first class support.

Uplink technology is certified by the ISO/IEC27001 information security management standard and backed by a web-based dealer support management tool.

For more information, visit the Uplink website at uplink.com.

Technical Specifications

COMPATIBLE ALARM PANELS	
Honeywell	Vista 15P and 20P (v4.0 and later)
DSC	PowerSeries
Interlogix	CADDX NetworX, Concord 4
RADIO INTERFACE	
Technology	UMTS/HSPA+/GSM/GPRS/EDGE
Frequency bands	850/1900 MHz
Sensitivity	-106 dBm (typical)
Output power	Class 4 (2W @ GSM 850 MHz, max) Class 1 (1W @ GSM 1900 MHz, max) Class 3 (0.25W @ UMTS 850/1900 MHz, max)
Antenna type	Internal (included) or external (not included)
POWER	
Power supply (not included)	12 VDC
Normal current	230 mA
Maximum current (peak)	2 A
ENVIRONMENTAL	
Temperature range	Operating: 32° to 104° F (0° to +40° C) Storage: 0° to 122° F (-17° to +50° C)
Humidity	0 to 90% RH, non-condensing
DIMENSIONS	
Height	6.25 inches
Width	4.0 inches
Depth	1.0 inches
Weight	1 lb
CERTIFICATIONS/COMPLIANCE	
EMC	FCC, IC, PTCRB, AT&T

Specifications subject to change without notice.

(888) 9-UPLINK | (888) 987-5465 | www.uplink.com | sales@uplink.com

A **Numerex** Solution

