

Horns



A High-Efficiency Horns

B For Industrial, Manufacturing, Warehouse Areas

- Very High-Efficiency Ensures Penetration w/Lower Energy Consumption
- Features Easy Omni-Lock I-Beam Clamp Mounting System
- Suitable for Indoor or Outdoor Installation
- Weather-Resistant

G High-Noise

Environments When You Really Need Power

- Higher Noise Environment
- Stainless Steel Hardware
- Weather-Resistant

Requires -48 Vdc, 1A or VP-2148D Power Supply for 2 Horns

H Paging In Two Directions

Bi-Directional Horn is Ideal for Long, Narrow Aisles

- Ideal for: Warehouses, Parking Lots, Complexes, Stadiums
- Stainless Steel Hardware
- Suitable for Indoor or Outdoor Installation
- Weather-Resistant

I Explosive Atmospheres

Safety-Assured for Explosive Atmospheres

- Solid Metal Housing
- Includes V-1092 Volume Control
- UL Listed For Use In: Class I, Groups C&D Gas Atmospheres

Accessory: Wire Cage

for Horns (2 Pack) ... V-WGHORN-2
for All Horns (Except Bi-Directional &
Explosion-Proof Horns)

19"H x 20.5"W x 17.5"D
(48.26cm x 52.07cm x 44.45cm)
7.05lbs (3.20kg)

D Marine Horns

E Resists Deteriorating Effects of Salt, Sun, High Humidity

- F**
- Equipped w/O-Ring Seals
 - Features Easy Omni-Lock I-Beam Clamp Mounting System
 - Suitable for Indoor or Outdoor Installation

Analog Horns		IP SoundPoints®	
High-Efficiency Horn		VPU	
A 5-Watt 3.6lbs (1.63kg)			
One-Way Beige.....V-1030C	-5	VIP-130AL-BGE*	
IP One-Way InformaCast® Beige.....V-1030C	-5	VIP-130AL-BGE-IC*	
One-Way Gray.....V-1030C-GY	-5	VIP-130AL-GY*	
IP One-Way InformaCast® Gray.....V-1030C-GY	-5	VIP-130AL-GY-IC*	
B 15-Watt 3.7lbs (1.68kg)			
One-Way Beige.....V-1036C	-15		
One-Way Gray.....V-1036C-GY	-15		
C Talkback 3.4lbs (1.5kg)			
Talkback Beige.....V-1048C	0	VIP-148AL-BGE*	
IP Talkback InformaCast® Beige.....V-1048C	0	VIP-148AL-BGE-IC*	
Talkback Gray.....V-1048C-GY	0	VIP-148AL-GY*	
IP Talkback InformaCast® Gray.....V-1048C-GY	0	VIP-148AL-GY-IC*	
7.38"H x 10.0"W x 10.4"D (18.75cm x 25.4cm x 26.42cm) IP Horns: 5.8lbs (2.63kg)			
Marine Horn			
D 5-Watt 3.7lbs (1.68kg)			
One-Way White.....V-1030M	-5	VIP-130AL-M*	
IP One-Way InformaCast® White.....V-1030M	-5	VIP-130AL-M-IC*	
E 15-Watt 3.7lbs (1.68kg)			
One-Way White.....V-1036M	-15		
F Talkback 3.5lbs (1.59kg)			
Talkback White.....V-1048M	0	VIP-148AL-M*	
IP Talkback InformaCast® White.....V-1048M	0	VIP-148AL-M-IC*	
7.38"H x 10.0"W x 10.4"D (18.75cm x 25.4cm x 26.42cm) IP Horns: 5.8lbs (2.63kg)			
G 30-Watt			
One-Way Beige.....V-1038	-15		
7.68"H x 12.25"W x 11.62"D (19.53cm x 31.12cm x 29.53cm) 4.1lbs (1.86kg)			
H Bi-Directional Horn			
One-Way Beige.....V-1050C	-6		
9.60"H x 8.20"W x 9.30"D (24.38cm x 20.83cm x 23.62cm) 6.3lbs (2.86kg)			
I Explosion-Proof Horn			
One-Way Gray.....V-1039A	-20		
6"H x 14"W x 17.5"D (15.24cm x 35.56cm x 44.45cm) 19lbs 8.62kg			
Talkback Gray.....V-1069A	0		
8"H x 14.6"W x 17"D (20.32cm x 37.08cm x 43.18cm) 19lbs (8.62kg)			

*Long Line Extender