



# SPECIFICATION SHEET

## 07-K200



### KUT-GARD® KNIT KEVLAR® GLOVE - LIGHT WEIGHT

- Kut-Gard®, 100% Kevlar®, light weight, 13 gauge
- Kevlar® yarn is designed to be cut resistant
- Seamless knit construction protects hands without sacrificing comfort or dexterity
- Kevlar® will not melt, ignite or conduct electricity
- Ambidextrous pattern
- Can be used as gloves or glove liners
- Color coded hems for easy size identification
- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel

### APPLICATIONS

- Automotive industry
- Light heat applications
- Glass operations
- Metal stamping

### CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry-cleaned. DO NOT BLEACH.

### TECHNICAL DATA

MATERIAL	100% Kevlar Fiber				
CONSTRUCTION	15 grams per glove for large, 1 ends 16/2CC yarn				
COLOR	Yellow				
CUFF STYLE	Elastic knit				
SIZES	XS - XL				
PACKAGING	12 pair per dozen; 12 dozen per case				
CASE	20.1" x 13.0" x 16.0" / 51cm x 33cm x 40.6cm				
CASE WEIGHT	XS	S	M	L	XL
	10.0 lbs / 4.5 kg	10.0 lbs / 4.5 kg	10.0 lbs / 4.5 kg	11.0 lbs / 5.0 kg	11.0 lbs / 5.0 kg
COO	USA				

### PERFORMANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

### BARCODES

ITEM	BAG	DOZEN	CASE
07-K200/XL	---	01616314003134	02616314003134
07-K200/L	---	01616314003127	02616314003127
07-K200/M	---	01616314003110	02616314003110
07-K200/S	---	01616314003103	02616314003103
07-K200/XS	---	01616314036750	02616314036750



### DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	7.5 / 19.1	8.0 / 20.3	9.0 / 22.9	9.5 / 24.1	10.0 / 25.4
B	4.0 / 10.2	4.0 / 10.2	4.0 / 10.2	4.25 / 10.8	4.7 / 12.0
H	Blue	White	Red	Yellow	Green

