



# SPECIFICATION SHEET

## 07-K300



### KUT-GARD® KNIT KEVLAR® GLOVE - MEDIUM WEIGHT

- Kut-Gard®, 100% Kevlar®, medium weight, 7 gauge
- Kevlar® yarn is designed to be cut resistant
- Seamless knit construction protects hands without sacrificing comfort or dexterity
- Kevlar® will not melt, ignite or conduct electricity
- Ambidextrous pattern
- Can be used as gloves or glove liners
- Color coded hems for easy size identification
- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel

### APPLICATIONS

- Automotive industry
- Light heat applications
- Glass operations
- Metal stamping

### CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry-cleaned. DO NOT BLEACH.

### TECHNICAL DATA

MATERIAL	100% Kevlar Fiber					
CONSTRUCTION	28 grams per glove for large, 2 ends 10/2CC yarn					
COLOR	Yellow					
CUFF STYLE	Elastic knit					
SIZES	XS - XXL					
PACKAGING	12 pair per dozen; 12 dozen per case					
CASE	20.0" x 13.0" x 16.0" / 50.8cm x 33cm x 40.6cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	13 lbs 5.9 kg	14 lbs 6.4 kg	17 lbs 7.7 kg	18 lbs 8.2 kg	19 lbs 8.6 kg	20 lbs 9.1 kg
COO	USA					

### PERFORMANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

### BARCODES

ITEM	BAG	DOZEN	CASE
07-K300/XS	---	01616314026720	02616314026720
07-K300/S	---	01616314003141	02616314036750
07-K300/M	---	01616314003158	02616314003103
07-K300/L	---	01616314003165	02616314003110
07-K300/XL	---	01616314003172	02616314003127
07-K300/XXL	---	01616314014895	02616314003134



### DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.5 / 21.6	9.0 / 22.9	10.0 / 25.4	10.5 / 26.7	11.0 / 27.9	11.5 / 29.2
B	3.5 / 8.9	3.6 / 9.1	4.0 / 10.2	4.1 / 10.4	4.3 / 10.9	4.5 / 11.4
H	Blue	White	Red	Yellow	Green	Black

