



SPECIFICATION SHEET

07-KA700



KUT GARD® SEAMLESS KNIT ACP / KEVLAR® BLENDED GLOVE WITH POLYESTER LINER – HEAVY WEIGHT

- Seamless knit construction provides comfort without sacrificing dexterity
- Proprietary ACP Technology and Kevlar® blended shell provides excellent protection against heat, cuts, lacerations and abrasions
- Heat resistance protects the hand from minor heat and burn injuries up to 350°F – do not use near open flame
- Polyester lining is ultra soft and very lightweight
- Knit wrist helps prevent dirt and debris from entering the glove
- 100% silicone free
- Cotton color binding denotes sizing
- Launderable for extended life and to reduce replacement costs

APPLICATIONS

- Sheet metal fabrication
- Canning & recycling
- Pulp & paper processing
- Plastic molding
- Assembly
- Painting

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using high speed. Tumble dry on low heat setting. Can be dry-cleaned. Do not bleach.

TECHNICAL DATA

MATERIAL	ACP Technology / Kevlar® / Polyester			
CONSTRUCTION	7 gauge			
COLOR	Green			
CUFF STYLE	Elastic knit			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 12 dozen per case			
CASE DIMENSIONS	20" x 13" x 16" / 50.8cm x 33cm x 40.6cm			
CASE WEIGHT	S	M	L	XL
	22 lbs 10 kg	23 lbs 10.4 kg	24 lbs 10.9 kg	25 lbs 11.3 kg
COO	USA			

PERFORMANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A5 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 4

BARCODES

ITEM	BAG	DOZEN	CASE
07-KA700/S	---	01616314125798	02616314125797
07-KA700/M	---	01616314125781	02616314125780
07-KA700/L	---	01616314125774	02616314125773
07-KA700/XL	---	01616314125804	02616314125803



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.0 / 22.9	10.0 / 25.4	10.4 / 26.7	10.9 / 27.9
B	3.6 / 9.1	4.0 / 10.2	4.1 / 10.4	4.3 / 10.9
H	White	Red	Yellow	Green

