



SPECIFICATION SHEET

08-K200PD



KUT-GARD® KNIT KEVLAR® GLOVE WITH SINGLE-SIDED PVC DOT GRIP - LIGHT WEIGHT 13 GAUGE

- Dupont Kevlar® fiber construction provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity
- Seamless knit construction protects hands without sacrificing comfort or dexterity
- Knit wrist helps prevent dirt and debris from entering the glove
- PVC dotted palm provides enhanced grip and extra cut and abrasion resistance
- Ambidextrous design allows replacing one glove at a time, rather than pairs
- Color coded cuffs to easily identify size

APPLICATIONS

- Glass handling
- Canning and bottling
- Sheet metal handling
- Recycling
- Automotive applications

CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spin extract using high speed. Tumble dry on Low to Medium heat setting. Can be Dry-Cleaned. DO NOT BLEACH.

TECHNICAL DATA

MATERIAL	Kevlar®, PVC			
COLOR	Shell: ■ Yellow, PVC Dots: ■ Blue			
CUFF STYLE	Elastic knit			
SIZES	S - XL			
PACKAGING	1 pair per bag, 12 pairs per dozen, 12 dozen per case			
CASE	20" x 13" x 16" / 50.8cm x 33cm x 40.6cm			
CASE WEIGHT (S-XL)	S	M	L	XL
	12 lbs / 5.4 kg	12 lbs / 5.4 kg	12 lbs / 5.4 kg	12 lbs / 5.4 kg
COO	USA			

PERFORMANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	BAG	DOZEN	CASE
■ 08-K200PD/S	----	01616314014949	02616314014949
■ 08-K200PD/M	----	01616314014956	02616314014956
■ 08-K200PD/L	----	01616314014963	02616314014963
■ 08-K200PD/XL	----	01616314014970	02616314014970



DIMENSIONS (in/cm)

	S	M	L	XL
A	8.0 / 20.3	9.0 / 22.9	9.5 / 24.1	10.0 / 25.4
B	4.0 / 10.2	4.0 / 10.2	4.25 / 10.8	5.0 / 12.7
H	■ White	■ Red	■ Yellow	■ Green

