



SPECIFICATION SHEET

100-2824

CLEANTEAM® SINGLE USE CLASS 10 CLEANROOM VINYL GLOVE WITH FINGER TEXTURED GRIP - 9.5"

- Exceed standards required for use in class 10 and other controlled environments
- Ambidextrous for quick and easy donning
- Powder-Free to reduce allergic reactions
- Beaded cuff adds additional strength to cuff edge for longer glove life and prevents liquid run-off
- Electrostatic Dissipative (ESD) for improved performance in electronics assembly

APPLICATIONS

- Electronics assembly
- Water manufacturing
- Pharmaceutical manufacturing
- Medical device manufacturing
- General cleanroom applications

TECHNICAL DATA

MATERIAL	Vinyl			
COLOR	☐ Clear			
SIZES	S-XL			
PACKAGING	100 per bag, 10 bags per case (1,000 pcs)			
CASE DIMENSIONS	12" x 10.4" x 12.6" / 30.5cm x 26.5cm x 32cm			
CASE WEIGHT	S	M	L	XL
	19 lbs / 8.6 kg	21 lbs / 9.5 kg	23 lbs / 10.4 kg	23 lbs / 10.4 kg
COO	China			

ELONGATION INFORMATION

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
10	350	10	350

BARCODES

ITEM	BAG	CASE
☐ 100-2824/S	01616314002182	02616314002182
☐ 100-2824/M	01616314002199	02616314002199
☐ 100-2824/L	01616314002205	02616314002205
☐ 100-2824/XL	01616314002212	02616314002212



DIMENSIONS (in/cm)

	S	M	L	XL
A	min 9.4 / 24	min 9.4 / 24	min 9.4 / 24	min 9.4 / 24
B	3.3 (+/- 0.2) / 8.5 (+/- 0.5)	3.7 (+/- 0.2) / 9.5 (+/- 0.5)	4.1 (+/- 0.2) / 10.5 (+/- 0.5)	4.5 (+/- 0.2) / 11.5 (+/- 0.5)

Palm Thickness 0.10 mm / Cuff Thickness 0.06 mm / Finger Tip Thickness 0.10 mm

