



SPECIFICATION SHEET

100-2830

SINGLE USE CLASS 10 CLEANROOM VINYL GLOVE WITH FINGER TEXTURED GRIP - 12"

- Exceed standards required for use in class 10 and other controlled environments
- Ambidextrous for quick and easy donning
- Powder-Free to reduce allergic reactions
- Beaded cuff adds additional strength to cuff edge for longer glove life and prevents liquid run-off
- Electrostatic Dissipative (ESD) for improved performance in electronics assembly

APPLICATIONS

- Electronics Assembly
- Wafer Manufacturing
- Pharmaceutical Manufacturing
- Medical Device Manufacturing
- General Cleanroom Applications

TECHNICAL DATA

MATERIAL	Vinyl			
COLOR	☐ Clear			
CUFF STYLE	Beaded Cuff			
SIZES	S - XL			
PACKAGING	100 pcs per inner; 10 inners per carton (1,000 pcs)			
CASE (IN/CM)	12.4 x 12.2 x 12.2 / 31.5 x 31 x 31			
CASE WEIGHT	S	M	L	XL
	23 lbs / 10.4 kg	11 lbs / 5 kg	25 lbs / 11.3 kg	30 lbs / 13.6 kg
COO	China			

PERFORMANCE PROPERTIES

Elongation Information:

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
10	350	10	350

BARCODES

ITEM	BAG	DOZEN	CASE
☐ 100-2830/S	01616314002229	---	02616314002229
☐ 100-2830/M	01616314002236	---	02616314002236
☐ 100-2830/L	01616314002243	---	02616314002243
☐ 100-2830/XL	01616314002250	---	02616314002250



DIMENSIONS (in/cm)

	S	M	L	XL
A	min 11.8 / 30	min 11.8 / 30	min 11.8 / 30	min 11.8 / 30
B	3.3 (+/- .2) / 8.3 (+/- .5)	3.7 (+/- .2) / 9.5 (+/- .5)	4.1 (+/- .2) / 10.5 (+/- .5)	4.5 (+/- .2) / 11.5 (+/- .5)

Palm Thickness: 0.10 mm
Cuff Thickness: 0.06 mm
Finger Tip Thickness: 0.10 mm

