



SPECIFICATION SHEET

10-KASCTOT



KUT GARD® SINGLE-PLY ACP™ / KEVLAR® BLENDED SLEEVE WITH THUMB HOLE

- The proprietary ACP / Kevlar® blend is exceptionally comfortable and offers twice the cut resistance compared with traditional Para-Aramid sleeves
- Heat resistant up to 400°F to protect arms from minor heat and burn injuries
- 100% silicone-free so it can be used in applications requiring a silicone free environment
- 100% Latex free
- Good washability, can be washed in soap and water and can be dry-cleaned
- Do not use near open flame

APPLICATIONS

- Automotive manufacturing
- Metal fabrication
- Sheet metal fabrication
- Painting
- Canning
- Recycling
- Assembly
- Plastic molding
- Glass handling
- Pulp and paper processing
- Food processing
- Metal stamping

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using high speed. Tumble dry on low heat setting. Can be dry-cleaned. Do not bleach.

TECHNICAL DATA

MATERIAL	ACP / Kevlar® Blend
CONSTRUCTION	Seamless knit
COLOR	Green
SIZES	24" (custom lengths available)
PACKAGING	144 each per case
CASE DIMENSIONS	12" x 18" x 12" / 30.5cm x 45.7cm x 30.5cm
CASE WEIGHT	13.2 lbs / 6 kg
COO	USA

CUT RESISTANT PROPERTIES

- ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)

BARCODES

ITEM	EACH	DOZEN	CASE
10-KA24SCTOT	616314197529	01616314197528	02616314197527



DIMENSIONS (in/cm)

	24"	---
A	24 / 61	---
B	3 / 7.6	---

