



SPECIFICATION SHEET

10-KS-TO SERIES



KUT-GARD® KEVLAR® SLEEVES, DOUBLE PLY, SEAMLESS RIB KNIT WITH THUMB HOLE

- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel
- Kevlar® yarn is designed to be cut resistant; will not melt, ignite or conduct electricity
- Double ply knit for added protection
- Blousy sleeve style offers loose fit to reduce fatigue
- ANSI/ISEA 105-2000 Level 3 cut resistance

APPLICATIONS

- Glass operations
- Metal stamping
- Sheet metal
- Automotive
- Electrical and light heat applications

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry-cleaned. Do not bleach!

TECHNICAL DATA

MATERIAL	100% Kevlar®	
CONSTRUCTION	Tube Knit	
COLOR	Yellow	
SIZES	14" or 18"	
PACKAGING	12 pairs per dozen, 12 dozen per case	
CASE DIMENSIONS	18.1" x 12" x 9.1" / 46cm x 30.5cm x 23cm	
CASE WEIGHT	14"	18"
	9 lbs / 4.1 kg	11.5 lbs / 5.2 kg
COO	USA	

CUT RESISTANT PROPERTIES

- ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 3

BARCODES

ITEM	DOZEN	CASE
10-KS14T0	01616314020209	02616314020209
10-KS18T0	01616314017056	02616314017056



DIMENSIONS (in/cm)

	14"	18"	
A	14 / 35.6	18 / 45.7	
B	3 / 7.6	3 / 7.6	

