



SPECIFICATION SHEET

120-4300



GUNNER™ WORKMAN'S GLOVE BY MAXIMUM SAFETY®

- Goatskin leather palm and half fingers provides the softest, most abrasion-resistant leather and is highly recommended for applications requiring tactile sensitivity
- PVC sandy grip on palm and thumbcrotch provides an enhanced grip and extra cut/abrasion resistance
- Spandex fabric back for comfort and breathability
- Synthetic leather fourchettes enhance the natural contour of the glove for a better fit
- Synthetic leather pull off hooks for easy on/off
- Micro cotton thumb for comfort
- Hook & loop closure for easy on/off and a secure fit
- Launderable for extended life and to reduce replacement costs
- Retail Ready

APPLICATIONS

- Light Construction
- Air Impact Tools
- Auto Repair
- Manufacturing
- Fabrication
- Landscaping

CARE INSTRUCTIONS

Machine wash in cold water. Do not bleach. Hang dry; tumble dry is not recommended. Do not iron.

TECHNICAL DATA

MATERIAL	Leather / Spandex / Polyester
CONSTRUCTION	Back: Foam laminated spandex fabric (96% polyester, 4% spandex) Palm: Goatskin leather, 0.7 - 0.8mm gauge Fingers: Synthetic leather (60% nylon, 40% polyurethane) Knuckles: Vinyl TPR mold
COLOR	■ Tan / ■ Black
CUFF STYLE	Hook and loop wrist closure
SIZES	S - XXL
PACKAGING	12 pairs per dozen, 6 dozen per case
CASE	15.7" x 11.8" x 10.2" / 40cm x 30cm x 26cm
CASE WEIGHT	9.4 lbs / 4.3 kg
COO	Pakistan

PERFORMANCE PROPERTIES

EN388: 2121						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	PAIR	DOZEN	CASE
■ 120-4300/S	616314069420	01616314069429	02616314069428
■ 120-4300/M	616314069413	01616314069412	02616314069411
■ 120-4300/L	616314069406	01616314069405	02616314069404
■ 120-4300/XL	616314069437	01616314069436	02616314069435
■ 120-4300/XXL	616314069444	01616314069443	02616314069442



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	6.2 / 15.7	6.5 / 16.5	6.8 / 17.3	7.1 / 18	7.3 / 18.5
B	3.75 / 9.5	4 / 10.2	4.25 / 10.8	4.5 / 11.4	4.75 / 12.1

Tolerance (in): +/- 0.125

