



SPECIFICATION SHEET

16-3400R



G-TEK® POLYKOR™ BLENDED GLOVE WITH DOUBLE-DIPPED NITRILE COATED MICRO-SURFACE GRIP

- Seamless construction offers increased comfort and breathability
- PolyKor™ shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Double-dipped nitrile micro-surface coating helps extend the life of the glove and provide excellent abrasion resistance
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Washable, resistant to chemicals, water, and ultraviolet light

APPLICATIONS

- Electronics
- Glass cutting
- Sheet metal handling
- General duty
- Parts assembly
- Sharp small parts handling

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	PolyKor™ Shell with Nitrile Micro-Surface Coating				
CONSTRUCTION	Seamless Knit				
COLOR	Shell: ■ Hi-Vis Orange / Coating: ■ Black				
CUFF STYLE	Continuous knit				
SIZES	S - XXL				
PACKAGING	1 pair per bag, 12 pair per dozen, 6 dozen per case				
CASE DIMENSIONS	14.2" x 11.8" x 12.6" / 36cm x 30cm x 32cm				
CASE WEIGHT	S	M	L	XL	XXL
	11.8 lb 5.4 kg	12.3 lb 5.6 kg	13.5 lb 6.1 kg	14 lb 6.4 kg	15 lb 6.9 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 4544 ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)
ASTM F1790-05 ANSI Cut Level 3

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5


BARCODES

ITEM	BAG	DOZEN	CASE
■ 16-3400R/S	----	01616314130754	02616314130753
■ 16-3400R/M	----	01616314130747	02616314130746
■ 16-3400R/L	----	01616314130730	02616314130739
■ 16-3400R/XL	----	01616314130761	02616314130760
■ 16-3400R/XXL	----	01616314130778	02616314130777



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.3 / 23.7	9.7 / 24.7	10.1 / 25.7	10.5 / 26.6	10.7 / 27.2
B	3.6 / 9.2	3.9 / 9.9	4.1 / 10.4	4.2 / 10.6	4.4 / 11.3
H	■ Red	■ Yellow	■ Brown	■ Black	■ Sky Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.