



SPECIFICATION SHEET

17-D200



KUT-GARD® KNIT DYNEEMA® GLOVE - LIGHT WEIGHT 13 GAUGE

- Seamless knit construction provides comfort without sacrificing dexterity
- Light weight Dyneema® shell provides excellent dexterity, tactile sensitivity and cut resistance
- Excellent for use as a glove liner
- Cotton color binding denotes sizing
- Made from component materials which comply with Federal regulations for food contact 21CFR 170-199

APPLICATIONS

- Food processing
- Can also be used as glove liners

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry or tumble dry low.

TECHNICAL DATA

MATERIAL	Dyneema®
CONSTRUCTION	13 gauge
COLOR	<input type="checkbox"/> White
CUFF STYLE	Continuous knit
SIZES	XS - XL
PACKAGING	12 pairs per dozen, 6 dozen per case
CASE	20.0" x 13.0" x 16.0" / 50.8cm x 33cm x 40.6cm
CASE WEIGHT	12.0 lbs / 5.4 kg
COO	USA



CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	BAG	DOZEN	CASE
<input type="checkbox"/> 17-D200/XL	---	01616314036811	02616314036811
<input type="checkbox"/> 17-D200/L	---	01616314036781	02616314036781
<input type="checkbox"/> 17-D200/M	---	01616314036798	02616314036798
<input type="checkbox"/> 17-D200/S	---	01616314036804	02616314036804
<input type="checkbox"/> 17-D200/XS	---	01616314036828	02616314036828

DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	7.0 / 17.8	7.5 / 19.1	9.0 / 22.9	9.5 / 24.1	10.0 / 25.4
B	3.5 / 8.9	3.5 / 8.9	4.0 / 10.2	4.0 / 10.2	4.25 / 10.8
H	<input checked="" type="checkbox"/> Blue	<input type="checkbox"/> White	<input checked="" type="checkbox"/> Red	<input checked="" type="checkbox"/> Yellow	<input checked="" type="checkbox"/> Green

