



SPECIFICATION SHEET

17-DL200



KUT-GARD® KNIT DYNEEMA®/LYCRA GLOVE - LIGHT WEIGHT 13 GAUGE

- Seamless knit construction provides comfort without sacrificing dexterity
- Light weight Dyneema® & Lycra shell provides excellent dexterity, tactile sensitivity and cut resistance
- Excellent for use as a glove liner
- Color coded hems for easy size identification
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199

APPLICATIONS

- Food processing
- Can also be used as glove liners

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry or tumble dry low.

TECHNICAL DATA

MATERIAL	Dyneema®, Lycra®
CONSTRUCTION	13 gauge
COLOR	☐ White
CUFF STYLE	Continuous knit
SIZES	XS - XL
PACKAGING	12 pairs per dozen, 6 dozen per case
CASE	20.0" x 13.0" x 16.0" / 50.8cm x 33cm x 40.6cm
CASE WEIGHT	70 lbs / 3.2 kg
COO	USA

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	BAG	DOZEN	CASE
☐ 17-DL200/XL	---	01616314036972	02616314036972
☐ 17-DL200/L	---	01616314036941	02616314036941
☐ 17-DL200/M	---	01616314036958	02616314036958
☐ 17-DL200/S	---	01616314036965	02616314036965
☐ 17-DL200/XS	---	01616314036989	02616314036989



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	6.0 / 15.2	6.5 / 16.5	7.0 / 17.8	7.5 / 19.1	8.0 / 20.3
B	3.25 / 8.3	3.25 / 8.3	3.75 / 9.5	3.75 / 9.5	4.0 / 10.2
H	☒ Blue	☐ White	☒ Red	☒ Yellow	☒ Green

